



Selectable colour temperatures help you to make the right choice

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 35W spots with a GU5.3 cap.

High quality light

Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Light beyond illumination

· Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

General

· Suitable For Accent Lighting: Yes

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Directional spot

Socket: GU5.3Dimmable: NoBulb Finish: ClearBulb Material: Plastic

Durability

• Number of switch cycles: 50,000

• Ambient temperature range: -20 °C to 45 °C

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- · Beam angle: 60 degree(s)
- · Color rendering index (CRI): 80
- Color temperature: 3000-4000-6500 K
- Nominal luminous flux: 360, 400, 400
- Warm-up time to 60% light: 0.5 s
- · Color Code: 3000/4000/6500
- Correlated Color Temperature (Nom): 3000, 4000, 6500 K
- Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

EAN: 8719514479012EOC: 871951447901200

 Product title: LEDSpot 35W DS ND MR16 12V 60D 1CT/6 AU

Power

• Power Factor (Fraction): 0.5

Power consumption

• Power factor: 0.5

Voltage: 12V AC electronic VWattage equivalent: 35 WPower Consumption: 4 W

Product dimensions and weight

Overall height: 45 mmOverall length: 45 mmOverall width: 50 mm

Rated values

Rated lifetime: 15,000Rated peak intensity: 330 cd

Technical specifications

Frequency: -Diameter: 50 mmDimmable: NoLine Frequency: -Cap-Base: GU5.3

Packaging dimensions and weight

• EAN/UPC - product: 8719514479012

Net weight: 0.03 kgGross weight: 0.04 kgHeight: 8.5 cm

Length: 5 cmWidth: 5 cm



Issue date: 2025-10-25 Version: 0.73 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips