



# 3.5 inch recessed downlight 8W

Go to your happy place with full-color WiZ downlights. Create the perfect ambience for every moment—whether focusing on work, partying down, or relaxing with your loved ones. Even light distribution eliminates dark spots and fills your room with dimmable, flicker-free light. Wi-Fi controllable, of course, using the WiZ app, WiZ remote, or your voice.

# **PRODUCT HIGHLIGHTS**

- Full color
- Cut out Ø90-100MM
- IP20(IP54 emitting surface)/Metal/Plastic/White

EAN: 8720169072251 wizconnected.com





#### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



## Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



## Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection.lt's simple. It's SpaceSense. It's WiZ.



#### Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



#### Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



## Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.

EAN: 8720169072251 wizconnected.com



## **SPECIFICATIONS**

#### **BULB CHARACTERISTICS**

Intended use: Indoor Lamp shape: Round

#### **DESIGN AND FINISHING**

Color: White

Material: Metal Plastic

#### **DURABILITY**

Average life (at 2.7 hrs/day): 25 year(s) Lumen maintenance factor: 70% Number of switch cycles: 15,000 Nominal lifetime: 25,000

#### EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable Dimmable with remote control: No LED integrated: Yes

Remote control included: No

#### **LIGHT CHARACTERISTICS**

Beam angle: 100 degree(s)
Color consistency: <5 SDCM
Color rendering index (CRI): ≥80
Color temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 100

Im/W

#### **MISCELLANEOUS**

Especially designed for: Living Room Kitchen Dining Room Bedroom

#### OTHER CHARACTERISTICS

Lamp current: 60 mA

#### **POWER CONSUMPTION**

Power factor: 0.5 Voltage: 220-240 V

#### PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.21 kg Recessed distance: 60 mm Overall height: 56 mm Overall length: 114 mm Overall width: 114 mm Recessed Ceiling cutout: 9.0 cm x 9.0

#### SERVICE

cm

Warranty: 2 year(s)

#### **TECHNICAL SPECIFICATIONS**

Diameter: 114 mm

Total lumen output fixture: 800 Light color: 2200-6500 (RGB) Fixture dimmable: No Wattage bulb included: 8

IP code: IP20(IP54 emitting surface) Class of protection: Class II - Double

Insulated

#### **WHAT'S SUPPORTED**

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date Max. number of accessories: 9999 Communication protocol: Bluetooth

WiFi (2.4GHz)

#### **PACKAGING DIMENSIONS AND WEIGHT**

EAN/UPC - product: 8720169072251

Net weight: 0.19 kg Gross weight: 0.23 kg Height: 12.6 cm Length: 7 cm

Width: 12.6 cm

### **Signify**

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: 8720169072251 wizconnected.com