



## 3.5 inch recessed downlight 8W

Go to your happy place with full-color WiZ downlights. Create the perfect ambience for every moment—whether focusing on work, partying down, or relaxing with your loved ones. Even light distribution eliminates dark spots and fills your room with dimmable, flicker-free light. Wi-Fi controllable, of course, using the WiZ app, WiZ remote, or your voice.

## PRODUCT HIGHLIGHTS

- Full color
- Cut out Ø90-100MM
- IP20(IP54 emitting surface)/Metal/Plastic/White



#### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




#### Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.

#### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



#### Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.

#### Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.

#### Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: Round

## DESIGN AND FINISHING

Color: White  
Material: Metal Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 15,000  
Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable  
Dimmable with remote control: No  
LED integrated: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Beam angle: 100 degree(s)  
Color consistency: <5 SDCM  
Color rendering index (CRI): ≥80  
Color temperature: 2200-6500 K  
Warm-up time to 60% light: 2  
Luminous Efficacy (rated) (Nom): 100  
lm/W

## MISCELLANEOUS

Especially designed for: Living Room  
Kitchen Dining Room Bedroom

## OTHER CHARACTERISTICS

Lamp current: 60 mA

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.21 kg  
Recessed distance: 60 mm  
Overall height: 56 mm  
Overall length: 114 mm  
Overall width: 114 mm  
Recessed Ceiling cutout: 9.0 cm x 9.0  
cm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Diameter: 114 mm  
Total lumen output fixture: 800  
Light color: Coloured and white light  
(RGBW)  
Fixture dimmable: No  
Wattage bulb included: 8  
IP code: IP20(IP54 emitting surface)  
Class of protection: Class II - Double  
Insulated

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: Wireless G  
Defined support period: Minimum of  
60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)  
Compatibility with 3rd party systems:  
Alexa Google Home IFTTT  
Klikaanklikuit Matter Samsung  
Smarthings Sonos

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072251  
Net weight: 0.19 kg  
Gross weight: 0.23 kg  
Height: 12.6 cm  
Length: 7 cm  
Width: 12.6 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.