



# State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

# Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- · Contains no mercury

# High quality LED light that lasts for decades

• Designed for the comfort of your eyes

# Highlights

#### No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won $\phi_{\overline{1}}$ t fade.

#### Contains no mercury



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

#### Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: E27Dimmable: NoBulb Finish: FrostedBulb Material: Plastic

#### **Durability**

• Number of switch cycles: 50,000

· Nominal lifetime: 12,000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

Beam angle: 150 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 3000 K

· Nominal luminous flux: 1700 lm

 Warm-up time to 60% light: instant full light

· Color Code: 830 | CCT of 3000K

 Luminous Efficacy (rated) (Nom): 113 lm/W

### Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

#### **Packaging information**

• EAN: 8720169187030

• EOC: 872016918703000

• Product title: ESS LEDBulb 15W E27

3000K 230V 1CT/12APR

# **Power consumption**

• Power factor: 0.5

Voltage: AC 220-240 VWattage equivalent: 120 W

• Power Consumption: 15 W

#### Product dimensions and weight

Overall height: 120 mmOverall length: 120 mmOverall width: 60 mm

# **Technical specifications**

• Frequency: 50-60

# Packaging dimensions and weight

• EAN/UPC - product: 8720169187030

Net weight: 0.04 kgGross weight: 0.06 kg

Height: 11.9 cmLength: 6.3 cmWidth: 6.3 cm



Issue date: 2025-11-01 Version: 0.119 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips