





# Enjoy a Beautiful garden with light, in a sustainable way

Philips Bustan Ultra Efficient outdoor lights use groundbreaking new technology to cut carbon emissions, reduce material waste, and lower energy usage. With an amazing lifetime of 50,000 hours, these lights last more than two times longer than Philips LED outdoor equivalents, and uses 50% less energy—just the thing for a more sustainable planet.

# Sustainable light solutions

- · Long lifetime up to 50,000 hours
- · Ultra Efficient
- · Up to 80 % energy saving

#### **Advanced LED light**

• 5 year warranty on LED system

# **Designed for outdoors**

• IP44 - weather proof

# **Special characteristics**

· Powerful light

# High quality light

• Warm white light 2700K

# Highlights

# Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

# **Ultra Efficient**



Consumes at least 50% less energy as compared with equivalent standard LED lights from Philips.

Up to 80 % energy saving



LED lights save up to 80% energy compared to a traditional lighting with the same light output. When you buy a Philips LED light, you start saving money right away. For each light source you replace with a LED light, you will see immediate returns on a lower energy bill.

# 5 year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

#### Powerful light

This Philips outdoor luminaire provides powerful light. A bright pool of light to light up your garden or terrace.

# Warm white light 2700K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces warm, relaxing light at 2700 K.

# Specifications

# Design and finishing

Color: AnthraciteMaterial: Metal

# **Durability**

· Nominal lifetime: 50,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- Day-and-night sensor: No
- · Fully weatherproof: Yes
- · LED integrated: Yes
- Motion sensor: No
- · Solar Energy: No
- · Centerpiece: No

#### Garden area

· Garden area: Garden & Patio

#### **Light characteristics**

- · Color rendering index (CRI): 80
- · Color temperature: 2700 K

# Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- · LED Innovations: UltraEfficient
- · Extra Features: Water Resistant

# **Power consumption**

• Power: 4.3

#### Product dimensions and weight

Net weight: 0.52 kgOverall height: 90 mmOverall length: 220 mmOverall width: 80 mm

#### **Service**

Warranty: 5 year(s)

#### **Technical specifications**

- Total lumen output fixture: 800Light color: Warm white light
- · Mains power: AC 220-240
- · Fixture dimmable: No
- · Energy class included light source: B
- Maximum wattage replacement bulb:
- IP code: IP44 | Wire-protected and splash-proof
- · Class of protection: Class I Earthed
- · Light source replaceable: Yes

# Packaging dimensions and weight

- EAN/UPC product: 8720169257252
- Net weight: 0.52 kgGross weight: 0.56 kg
- Height: 22.5 cm
- · Length: 8.5 cm
- Width: 9.9 cm



Issue date: 2025-12-06 Version: 0.314 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips