

# PHILIPS

Spot 60W R7S R7S

LED

4000K

1000lm

15000h



8720169301917



## Bright LED lighting with excellent light quality

This innovative Linear LED is the perfect replacement for halogen R7S lamps, while far surpassing them in terms of energy efficiency.

### High quality light

- Cool, white light

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen linear

### Choose for a sustainable solution

- Saves up to 80% Energy

# Highlights

## Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

## Replaces linear halogen



With its beautifully shaped design and familiar dimensions, this standard modern lighting, LED linear is the perfect sustainable replacement for traditional halogen linears.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## General

- Suitable For Accent Lighting: No

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: R7s
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Clear Plastic

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Guarantee

- Warranty period: 2 years

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1000 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 4000
- Luminous Flux: 1,000 lm
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 142

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8720169301917
- EOC: 872016930191700
- Product title: LED 60W R7S 78mm CW ND 1PF SRT4

**Power**

- Power Factor (Fraction): 0.5

**Power consumption**

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 60
- Energy Efficiency Label (EEL): D
- Power: 7
- Energy Consumption kWh/1000 h: 7

**Product dimensions and weight**

- Overall height: 78 mm
- Overall length: 78 mm
- Overall width: 28 mm

**Technical specifications**

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 1932589
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM) - Flickering value as per EN 61000-3-3: 1
- Cap-Base: R7s
- can it be used in closed luminaires: No

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169301917
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 12.7 cm
- Length: 3 cm
- Width: 6.3 cm



Issue date: 2026-04-15  
Version: 0.268

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)