

PHILIPS

Filament Bulb Frosted
60W A60 B22

UltraEfficient

4000K

840lm

50000h

8720169394254



UltraEfficient lamp, our most energy efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

Choose for a sustainable solution

- Saves over 50% energy (Bulb)

Designed to last longer and save more energy

- Long life bulb – Lasts up to 50 years

Highlights

Saves over 50% energy (Bulb)



Enjoy the energy-savings of LEDs without sacrificing light quality.

Instantly save over 50% in energy compared to standard Philips LED bulbs.

Long life bulb - Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 840 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 4000 K
- Luminous Flux: 840 lm
- Luminous Efficacy (rated) (Nom): 210 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8720169394254
- EOC: 872016939425400
- Product title: LED CLA 4W A60 B22 4000K FR UE SRT6

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage equivalent: 60 W
- Power Consumption: 4 W

Product dimensions and weight

- Overall height: 102 mm
- Overall length: 102 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50-60
- Diameter: 60 mm
- Dimmable: No
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC – product: 8720169394254
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 12.2 cm
- Length: 6.4 cm
- Width: 6.6 cm



Issue date: 2025-08-30
Version: 0.82

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com