



UltraEfficient lamp, our most energy efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

Choose for a sustainable solution

· Saves over 40% energy (Bulb)

Designed to last longer and save more energy

· Long life bulb - Lasts up to 50 years

Highlights

Saves over 40% energy (Bulb)



Enjoy the energy-savings of LEDs without sacrificing light quality.

Instantly save over 40% in energy compared to standard Philips LED bulbs.

Long life bulb - Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: B22Dimmable: NoBulb Finish: FrostedBulb Material: Glass

Durability

Number of switch cycles: 50,000Ambient temperature range: -20 to

+45 °C

· Nominal lifetime: 50,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 300 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 2700 K

• Nominal luminous flux: 1535 lm

• Warm-up time to 60% light: 0.5 s

• Correlated Color Temperature (Nom):

· Luminous Flux: 1,535 lm

Luminous Efficacy (rated) (Nom): 210 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: UltraEfficient

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8720169394315

• EOC: 872016939431500

 Product title: LED CLA 7.3W A60 B22 2700K FR UE SRT6

Power

• Power Factor (Fraction): 0.4

Power consumption

• Power factor: 0.4

Voltage: AC 220-240 VWattage equivalent: 100 WPower Consumption: 7.3 W

Product dimensions and weight

Overall height: 102 mmOverall length: 102 mmOverall width: 60 mm

Technical specifications

Frequency: 50-60Diameter: 60 mmDimmable: NoCap-Base: B22

Packaging dimensions and weight

• EAN/UPC - product: 8720169394315

Net weight: 0.04 kgGross weight: 0.07 kgHeight: 12.2 cm

Length: 6.4 cmWidth: 6.6 cm



Issue date: 2025-11-01

Version: 0.82

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips