



Selectable colour temperatures help you to make the right choice

Enjoy 5 possible light colors in one product. Change the color of your light easily with by switching the button on the product.

High quality light

• Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Light beyond illumination

· Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

General

Suitable For Accent Lighting: Yes

· Intended use: Indoor/Outdoor

Bulb characteristics

Lamp shape: Directional reflector
Socket: E27
Dimmable: No
Bulb Finish: Clear
Bulb Material: Plastic

Durability

• Number of switch cycles: 50,000

• Nominal lifetime: 15,000

• Ambient temperature range: -20 to $+45\,^{\circ}\mathrm{C}$

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- · Beam angle: 100 degree(s)
- · Color rendering index (CRI): 80
- · Color temperature:

2700-3000-4000-5000-6500 K

- · Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 2700, 3000, 4000, 5000, 6500 K
- · Luminous Flux: 1,200 lm
- Luminous Efficacy (rated) (Nom): 100 lm/W

Instant on

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8721103071033

• EOC: 872110307103300

• Product title: LEDPAR38 12W E27 DS

FR ND IP65 1CT/6

Power

• Power Factor (Fraction): 0.5

Power consumption

• Power factor: 0.5

Voltage: AC 220-240 VWattage equivalent: 120 WPower Consumption: 12 W

Product dimensions and weight

Overall height: 13.3 mmOverall length: 13.3 mmOverall width: 12 mm

Technical specifications

Frequency: 50-60Dimmable: NoCap-Base: E27

Packaging dimensions and weight

• EAN/UPC - product: 8721103071033

Net weight: 0.13 kg
Gross weight: 0.2 kg
Height: 13.6 cm
Length: 12.4 cm
Width: 12.4 cm



Issue date: 2025-11-22 Version: 0.85 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V