

# PHILIPS

Halogen capsule  
bulb

40 W

G9 cap

Frosted

8727900822038



## Superior halogen lighting

Provides bright sparkling light with best dimmability and compact size. It's easy fit in modern and open luminaries. No need of transformer, perfect and easy for creating imaginative lighting without compliment the style.

### **Personal scene setting**

- Best dimmiablity to dims and create a cosy atmopshere

### **Create a cosy atmosphere**

- Bright halogen light provides better contrast for more focus
- Bright, sparking lighting to create your light scene at home

### **Free to be used in open luminary**

- Small size easily fits in modern, style light fixtures

# Highlights

## Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

## Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

## Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

## Small size

The capsule gives high-intensity light with a clearly directional beam in an extremely small size. It is perfect for modern and stylish light fixtures at home.

# Specifications

## Bulb characteristics

- Shape: Capsule
- Socket: G9
- Bulb Finish: Frosted
- Dimmable: Yes

## Bulb dimensions

- Height: 21.7 mm
- Width: 12.75 mm

## Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Nominal lifetime: 2,000

## Light characteristics

- Application: Special application
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Nominal luminous flux: 370 lm
- Luminous Flux: 460 lm
- Luminous Efficacy (rated) (Nom): 11.5

## Power consumption

- Voltage: 240 V
- Power: 40

## Rated values

- Rated lifetime: 2,000

## Technical specifications

- Cap-Base: G9

## Packaging dimensions and weight

- EAN/UPC - product: 8727900822038
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 12.3 cm
- Length: 1.7 cm
- Width: 7.4 cm



Issue date: 2026-03-31  
Version: 0.488

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)