



Lumec **Optima** LED post top and pendant luminaires are the perfect choice for urban projects such as streets, walkways and public spaces that compel that extra little bit of detail. This timeless luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment. Paired with the latest LED technology, its IP66 rating, multiple lumen outputs, various luminaire style options and energy-saving control options are well suited to meet wide range of project requirements.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

example: OT10-72W32LED3K-G3-ACDR-LE3A-120-DMG-RC-GN8TX

Series	LED module	CCT	Gen. G3	Optical system	Voltage	Driver options	Options				Poles/ Brackets	Finish
							Receptical	Control	Luminaire	Decorative		
OT10 OT20	35W32LED 55W32LED 72W32LED 55W48LED ⁸ 80W48LED 70W64LED	2.2K ⁹ 2200K 3K 3000K 4K 4000K	G3 Gen3	ACRD-LE2A Type II (ASYM) with acrylic globe ACRD-LE3A Type III (ASYM) with acrylic globe ACRD-LE4A Type IV (ASYM) with acrylic globe LE2F Type II (ASYM) w/flat glass lens LE2F Type II (ASYM) w/flat glass lens LE2S Type II (ASYM) w/sag glass lens LE3F Type III (ASYM) w/flat glass lens LE3S Type III (ASYM) w/sag glass lens LE4F Type IV (ASYM) w/flat glass lens LE4S Type IV (ASYM) w/sag glass lens LE5F ² Type V (SYMM) w/flat glass lens LE5S ² Type V (SYMM) w/sag glass lens	UNV 120V-277V 347 480	DMG 0-10V SRD ¹ Sensor ready driver, standard configuration SRD1 ¹ Sensor ready driver, alternate configuration	RC ^{3,5} Receptacle for twist-lock photo cell or shorting cap, 3-pins RCD7 ^{3,5} Receptacle for twist-lock photo cell or shorting cap, 7-pins	PH8 ⁶ Twist-lock Photoelectric Cell PH9 ⁶ Shorting cap PHXL ^{1,6} Twist-lock Photoelectric Cell extended life, UNV (120- 277VAC)	HS House Side Shield SP2 20kV / 10kA Surge protector TN2.875C Fitter to fit over a 2 7/8" (73 mm) O.D by 4" (102 mm) long tenon TN3 Fitter to fit over a 3" (76 mm) O.D by 4" (102 mm) long tenon TN3.5 Fitter to fit over a 31/2" (89 mm) O.D by 4" (102 mm) long tenon	DA Decorative arches DC Decorative cap DF10 ⁴ Decorative Coupola DF20 ⁴ Decorative Coupola FN1 ^{4,7} Decorative finial FN2 ^{4,7} Decorative finial FN3 ^{4,7} Decorative finial FN5 ^{4,7} Decorative finial FN6 ^{4,7} Decorative finial FN8 ^{4,7} Decorative finial FN9 ^{4,7} Decorative finial FN10 ^{4,7} Decorative finial FNC ^{4,7} Decorative finial painted copper	Consult with Signify. com/ outdoor luminaires for details and the complete line of Signify poles and brackets.	Textured BE2TX Midnight Blue BE6TX Ocean Blue BE8TX Royal Blue BG2TX Sandstone BKTX Black BRTX Bronze GN4TX Blue Green GN6TX Forest Green GN8TX Dark Forest Green GNTX Green GY3TX Medium Grey RD2TX Burgundy RD4TX Scarlet WHTX White Other GR Gray Sandtex NP Natural Aluminum TG Hammer- tone Gold

1. Not available 347-480 volt.

2. Not available with HS option.

3. Use of photoelectric cell or shorting cap is required to ensure proper illumination.

4. Not available with RCD7 and RC.

5. The RCD7 is located on top of the roof in place of the finial for use with a control node.

6. RC or RCD7 must be selected for this option.

7. Not available with DF10 or DF20.

8. Not available with SRD or SRD1.

9. Extended lead-time may apply (consult factory).