



046677585785



Light up your outdoor life

This Philips Alula solar portable light has 3 in 1 light setting modes. By simple knock or tap you can enjoy two brightness level or RGB party mode.

Sustainable light solutions

· Long lifetime up to 15,000 hours

Advanced LED light

· High quality LED light

Premium quality

· High quality material

Highlights

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while having the perfect light ambiance in your home.

High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

High quality material



This Philips outdoor lamp is made of high quality materials with superior finishing. This ensures a solid and long lasting product which is resistant to corrosion and stains in all weather conditions

Specifications

Design and finishing

Color: BlackMaterial: Plastic

Durability

• Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- · Day-and-night sensor: No
- Fully weatherproof: Yes
- · LED integrated: Yes
- Motion sensor: NoSolar Energy: Yes
- · Warm White Light: No
- · Centerpiece: Yes

Garden area

· Garden area: Garden & Patio

Light characteristics

Color rendering index (CRI): 80Color temperature: 3000 K

Miscellaneous

- Especially designed for: Garden,
 - Patio
- Style: Contemporary
- · Type: Portable Lights
- · EyeComfort: No
- Extra Features: RGB Colors, Water Resistant

Product dimensions and weight

- Net weight: 0.362 kg
- Overall height: 149 mm
- · Overall length: 131 mm
- · Overall width: 120 mm

Service

· Warranty: 2 year(s)

Technical specifications

• Total lumen output fixture: 80/20

Light color: 3000Mains power: 4 VFixture dimmable: No

• Energy class included light source:

not applicable

 $. \ Maximum \ wattage \ replacement \ bulb:$

1.2

IP code: UL03 | Wet LocationClass of protection: Class III - Safe

Extra Low Voltage

· Light source replaceable: No

Packaging dimensions and weight

• EAN/UPC - product: 046677585785

Net weight: 0.36 kgGross weight: 0.44 kgHeight: 12 cm

Length: 14 cmWidth: 15 cm



Issue date: 2025-09-10 Version: 0.122 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips