

PHILIPS

Crust Ground
Spots/Spike 3.2W

myGarden

2700K

Inox

Water Resistant



17356/47/P0



Illuminate your garden at night

This solid Philips myGarden Crust LED recessed spot in stainless steel marks out paths and driveways without changing the look of your garden. Premium materials and high-quality Philips LEDs ensure almost zero maintenance once installed.

Sustainable light solutions

- Energy saving
- High quality LED light

Bring design into your garden

- High quality stainless steel and superior synthetics

Advanced light for outdoors

- Philips offers 5 year warranty on the LED module and driver

Special characteristics

- Easy installation
- IP67 – weather proof
- Long operating life

Highlights

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light

The LED light bulb, delivered with this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality stainless steel and superior synthetics.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Easy installation



Installing a luminaire can be sometimes difficult, with this Philips outdoor lamp, you can be sure that high attention has been given to facilitate it and simplify it for you. This article is delivered with a torx key to used during installation.

IP67 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP67: it is protected against temporary immersion and ideal for lighting paths or driveways. You can even drive over it.

Long operating life



Philips LED lights offer an average of up to 25,000 hours (which equals an average of 25 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycle).

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Color: Stainless steel
- Material: Stainless Steel

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti rust anti dust: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Solar Energy: No

Garden area

- Garden area: Garden & Patio

Light characteristics

- Color rendering index (CRI): 80
- Luminous Efficacy (rated) (Nom): 112 lm/W

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Ground Spots/Spikes
- EyeComfort: No
- Extra Features: Water Resistant

Power consumption

- Wattage: 3.2 W

Product dimensions and weight

- Net weight: 0.334 kg
- Cut out length: 10.5 cm
- Cut out width: 10.5 cm
- Length: 12 cm
- Recessed distance: 12 mm
- Width: 12 cm
- Overall height: 126 mm
- Overall length: 115 mm
- Overall width: 115 mm
- Recessed Ceiling cutout: 10.5 cm x 10.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 350
- Light color: 2700
- Mains power: AC 220-240
- Energy class included light source: F
- Wattage bulb included: 3 W
- IP code: IP67 | Dust-tight and temporary immersion-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8718696159019
- Net weight: 0.33 kg
- Gross weight: 0.43 kg
- Height: 12.6 cm
- Length: 12.1 cm
- Width: 12.1 cm



Issue date: 2025-09-13
Version: 0.427

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com