

# PHILIPS

Stick energy saving  
bulb

Essential

18 W (100 W)

E27 cap

Cool daylight

8718291777991



## Best value for money

Philips EcoHome bulbs offer great value for money. Realize energy savings of up to 80% over old incandescent bulbs with these reliable and affordable replacements.

### Sustainable choice

- Save energy from the moment you turn the switch

### Beacon of trust

- You can trust what the Philips packaging is saying

# Highlights

## Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy

bill. The level of energy saving differs per lamp type and technology.

## Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

# Specifications

## Bulb characteristics

- Shape: Stick
- Socket: E27
- Dimmable: No

## Durability

- Average life (at 2.7 hrs/day): 4 year(s)
- Nominal lifetime: 8,000

## Light characteristics

- Application: Just light, Extra brightness
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1100 lm

## Power consumption

- Voltage: 220-240 V
- Wattage equivalent: 100 W
- Power Consumption: 18 W



Issue date: 2025-08-02  
Version: 0.546

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)