

PHILIPS

Squire table lamp

Smart LED

Full color

Dual zone light effect

Easy plug and play



8719514396999



Easy to control, full-color smart table lamp

Bring smart light to any corner of your space with the WiZ Squire dual zone table lamp, which casts colorful light onto the wall. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi setups.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules
- Preset wellbeing features

Light modes

- Millions of colors and dynamic light modes
- Customize Scenes with preset dynamic light modes
- Subtle backlight design for unique look


Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Preset wellbeing features



Use the preset wellbeing features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm through the day. WiZ will provides you bright daylight when you need to get energized and focus, and transition smoothly to soft warm white to help you relax and sleep better.

Millions of colors and dynamic light modes




Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

Customized Scenes



Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, remote or voice.

Dual zone light effect



This lamp's unique dual-light-zone design lets you project a splash of light onto the wall, while still emitting a soft glow onto the table or counter on which the light sits.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- Nominal lifetime: 25,000

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: Yes
- LED integrated: Yes
- On/off switch on wire: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): ≥ 80
- Color temperature: 2200–6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 68 lm/W

Miscellaneous

- Especially designed for: Living Room, Dining Room, Bedroom, Children's room
- EyeComfort: Yes

Other characteristics

- Lamp current: 300 mA

Power consumption

- Power factor: 0.4
- Voltage: 100–240 V

Product dimensions and weight

- Net weight: 0.68 kg
- Overall height: 134 mm
- Overall length: 134 mm
- Overall width: 134 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 134 mm
- Total lumen output fixture: 620
- Light color: 2200–6500 (RGB)
- Wattage bulb included: 9
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

What's supported

- Compatible with Effects: Yes
- WiFi: Wireless G
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Communication protocol: Bluetooth, WiFi (2.4GHz)

Packaging dimensions and weight

- EAN/UPC – product: 8719514396999
- Net weight: 0.68 kg
- Gross weight: 0.76 kg
- Height: 15 cm
- Length: 13.5 cm
- Width: 13.5 cm



Issue date: 2025-08-30
Version: 0.122

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com