

# PHILIPS

## Cicero Portable Light

Portable Lights

5000K

Black

Dimmable



8719514443730



## Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

### Premium quality

- EyeComfort - light that's easy on the eyes

# Highlights

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria

including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that

way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round
- Dimmable: Yes

## Design and finishing

- Color: Black
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 30,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 30 lm/W

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Portable Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 1200 mA

## Product dimensions and weight

- Net weight: 0.36 kg
- Overall height: 198 mm
- Overall length: 115 mm
- Overall width: 115 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 115 mm
- Total lumen output fixture: 180
- Light color: 5000
- Mains power: 5 V
- Wattage bulb included: 6
- IP code: IP54 | Dust-accumulation-protected and splash-proof
- Class of protection: Class III - Safe Extra Low Voltage



Issue date: 2025-08-30  
Version: 0.356

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)