



## String Lights

Make your home vibrant with a range of colors that you can adjust to make special moments even more memorable. Use with your existing Wi-Fi to control with the WiZ app or your voice.

## PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- Outdoor rated




### Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



### Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



### Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



### Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



### Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



### Low-voltage technology and easy installation

Designed for outdoor enjoyment! No complicated wiring or special installation required—just plug it in and go. If you want to change the light's location, just unscrew the adapter and move it somewhere else.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Outdoor  
Lamp shape: Rectangle  
Dimmable: Yes

## DESIGN AND FINISHING

Color: Black  
Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable  
Dimmable with remote control: Yes  
LED integrated: Yes  
LED lamp(s) included: Yes  
On/off switch on wire: Yes  
Power adapter included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Color consistency: 7 SDCM  
Color rendering index (CRI):  $\geq 80$   
Color temperature: 2700-5000 K  
Warm-up time to 60% light: 2  
Luminous Efficacy (rated) (Nom): 10  
lm/W

## MISCELLANEOUS

Especially designed for: Garden  
Balcony

## OTHER CHARACTERISTICS

Lamp current: 200 mA

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 2.15 kg  
Overall height: 200 mm  
Overall length: 14,800 mm  
Overall width: 45 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Lumen output bulb included: 10  
Total lumen output fixture: 120  
Light color: 2700-5000 (RGB)  
Wattage bulb included: 12  
Maximum wattage replacement bulb: 12  
IP code: IP65 (Adaptor IP44)  
Class of protection: Class II - Double Insulated  
Light source replaceable: Yes  
Number of light sources: 12

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514554450  
Net weight: 2.14 kg  
Gross weight: 2.54 kg  
Height: 33 cm  
Length: 12.7 cm  
Width: 39.4 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.