



Bright LED lighting with excellent light quality

LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

Designed for the comfort of your eyes

Choose for a sustainable solution

- · Saves up to 90% Energy
- · Long life bulb Lasts up to 50 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: E27Dimmable: NoBulb Finish: FrostedBulb Material: Glass

Bulb dimensions

Height: 10.4 cmWidth: 6 cm

Durability

Number of switch cycles: 50,000Nominal lifetime: 50,000 hour(s)

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 80

· Color temperature: 6500 K

· Nominal luminous flux: 1500 lm

• Warm-up time to 60% light: instant full light

· Color Code: 865 | CCT of 6500K

Miscellaneous

EveComfort: Yes

 LED Innovations: UltraEfficient, EveComfort

Other characteristics

· Efficacy: 200 lm/W

Packaging information

· EAN: 8720169205581

• EOC: 872016920558100

 Product title: LED CLA A60 7.5W E27 6500K FR UE1CT/12

Power consumption

• Power factor: 0.5

Voltage: AC 220-240 V

· Wattage: 7.5 W

· Wattage equivalent: 100 W

Product dimensions and weight

· Length: 10.4 cm

Technical specifications

• Frequency: 50-60 Hz



Issue date: 2025-03-07 Version: 0.166 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips