

# PHILIPS

Double  
Telephone Socket

Switches & Sockets

LeafStyle

White

PC

8719514389144



## Aesthetic appearance to enhance interior design

Philips provides modern design and high safety standard switches & sockets for your home

### **Safety and Durability**

- High quality PC
- Pass Philips internal rule

# Highlights

## High quality PC

High quality PC for Cover and Base.

## Pass Philips internal rule

Pass strict Philips internal design rule.

# Specifications

## Design and finishing

- Color: White
- Material: PC
- Module/Gang: 2 Module
- Socket/connector Type: RJ11
- Product Range: LeafStyle
- Minimum Installation Box Depth: 4.5 cm

## Durability

- Number of Operation Cycles: 750

## Product dimensions and weight

- Length: 8.74 cm
- Width: 9.34 cm
- Depth: 2.64 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Frequency: - Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514389144
- Net weight: 0.1 kg
- Gross weight: 0.1 kg
- Height: 4 cm
- Length: 8.7 cm
- Width: 9.3 cm
- Material number (12NC): 913715120608



Issue date: 2024-08-12  
Version: 0.18

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)