

Philips Ledinaire Floodlight Solar gen2

Ready for
any job.
Powered by
the sun.



PHILIPS

The next generation of our 100% solar floodlight—improved just for you.

We know that simplicity, flexibility, and reliability are key for getting every job done right and on time. That's why Philips Ledinaire Floodlight Solar gen2 offers three CCTs in one luminaire, easily selectable on-site. Add new ease-of-use features and an improved product architecture, and you've got the ideal solar floodlight for a wide range of residential and commercial applications—your dependable and affordable choice for every job.

Reduce inventory and adapt to any project

- 3 CCTs (3000 K / 4000 K / 6500 K) in each luminaire
- Easily switch between CCTs on site

Install more quickly than ever

- No wiring or electrical work required
- Simply plug in solar panel using included 5m cable

Save more energy

- Automatic dusk-to-dawn operation
- PIR motion sensor for responsive, energy-efficient operation


Rely on the benefits of an improved product architecture

- Robust aluminum housing ensures durability
- Openable battery box for easy replacement and repair
- USB-C charging available to guarantee uptime

Enjoy improved ease-of-use

- LED indicator shows battery charge level
- Change CCT and select motion detection and constant lighting modes with convenient remote control

Wide range of applications



a lighting brand of  Signify

Your benefits



Freedom from the grid

100% powered by the sun



Simple installation

Install anywhere—no wiring or electrical work required



All-in flexibility

Multiple CCTs in each luminaire



Improved durability

Robust aluminum housing with IP66 rating




Easy to configure and use

Remote control, openable battery box, battery charge indicator



Long lifetime

75,000 hrs (L₇₀)



Philips Ledinaire Floodlight Solar gen2 3-in-1 product codes.

Product designation	Lumens (lm)	CCT (K)	Lifetime (hrs)	Efficacy (lm/W)	12NC	EAN1	EOC
VVP085 G2 22_24S/830_40_65 SLR MDU	2200 –2400	3000 / 4000 / 6500	75K (L ₇₀)	160	911401838203	8721103705761	872110370576199
VVP085 G2 44_48S/830_40_65 SLR MDU	4400 –4800	3000 / 4000 / 6500	75K (L ₇₀)	160	911401838303	8721103705778	872110370577899

Proven quality. Effortless installation. Every time.

Philips Ledinaire: Your dependable and affordable choice for every job.

Get all product info and configuration options in the [online catalog](#)



© 2026 Koninklijke Philips N.V. All rights reserved.
www.philips.com

a lighting brand of ignify