

# Stonco

by  Signify

## Special Purpose

Roughlyte

Pendant mount, incandescent



Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

Stonco Roughlyte is available in wattages ranging from 100 to 200. Applications include wall, columns, ceilings and canopies in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

### Ordering guide

Example: VP11GC

Series	Wattage	Lens
<input type="text" value="VP"/>		
VP Pendant mount	11 100W 21 200W	GC Glass globe and cast guard

### Product Specifications

- All incandescent Roughlyte ceiling and wall fixtures are not supplied with a lamp. This fixture requires a medium base incandescent A lamp. The lamp can be clear or coated.
- Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only).
- cULus listed for wet locations.
- **Not recommended for use in hazardous locations.**


# VP Roughlyte pendant mount

## VP

- Top hub tapped 1/2" NPT.
- Heat and shock resistant glass globe.
- Sockets are pre-wired with extra long 1/2" stripped leads.

## Dimensions

Catalog No.	Height (H)	Dia. (D)
VP11GC	9-3/4"	4-5/16"
VP21GC	10-7/8"	5-5/16"



## Accessories



### 4" Round boxes

Die-cast aluminum for use with conduit, Stonco ceiling, surface and wall fixtures and flood lights. Four side and one back hole tapped 3/4" as shown. Heavy-duty gasket, screws, four aluminum five-threaded plugs. No cover.

Catalog No.	Tap size	Description
VXL13	3/4"	Mounting box



V131  
Cast Aluminum Guard

### Guards

Cast aluminum guards are twist on/off bayonet type, includes allen head security screws. Shipped with threaded ring adapter for use with standard threaded bases or the new RoughLyte bases.

Catalog No.	Cast guard Fits globe diameter
V131	3-1/2"



VGC100  
Clear Glass Globe



VGP100  
Clear Prismatic Globe



VGR100  
Ruby Glass Globe



VPRC10  
Prismatic Lexan Globe

## Colored and specialty globes

Full molded threads. Fit all Stonco housings. Globes for vertical mounting only.

Catalog No.	Description	Catalog No.	Description
<b>3-1/2" Globe dia.</b> <b>Height - 6 11/16"</b>	<b>Glass</b>	<b>4-3/8" Globe dia.</b> <b>Height - 8 3/8"</b>	<b>Glass</b>
VGC100	Clear*	VGC200	Clear*
VGP100	Clear, prismatic		
VGA100	Amber (60W max.)		
VGB100	Blue (60W max.)		
VGR100	Ruby (60W max.)		
<b>3-1/2" Globe dia.</b>	<b>LEXAN</b>	<b>4-3/8" Globe dia.</b>	<b>LEXAN</b>
VPRC5	Clear, prismatic (60W Max.)	VPRC10	Clear, prismatic (75W Max.)

\*Standard with all incandescent glass fixtures.

**NOTE:** Use of colored globes will down-rate wattage.

