

PHILIPS

Table lamp

66049GADWALL BC

white

LED



66049/31/H5



Advanced desk lighting for a brighter future

Enjoy flexibility with Philips Gadwall BaseClamp LED desklight with dual uses of clamp or base. Honeycomb lenses diffuse light that is even with less glare, while 4-level step dimming allows adjustability for a good reading atmosphere.

Easy to Experience

- Adjustable light angle

Advanced LED light

- Adjustable light intensity with dimmer switch

Energy saving

- 80% energy saving, compared to traditional light sources
- Built-in LED, as part of the system

Premium quality


- Die-casted aluminum for a premium look and feel

Lighting for healthy eyes

- Scientific light setting for optimum eye care

Highlights

Adjustable light angle Dimmable



Adjust the light intensity of the Philips LED lights with a dimmer switch (not included). This makes this light ideal for creating an ambience for any occasion, whether a cosy meal ? deux or chilling out with family and friends in your living room. Philips tested a number of wall dimmers that have proved to be compliant with our LED lights. A list of compatible dimmers is available in the downloads and support section.

80% energy saving



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambience in your home.

Premium materials



Scientific light setting



Specifications

Design and finishing

- Color: White
- Material: Aluminium

Extra feature/accessory incl.

- FFP - Frustration Free Pack: Yes

Miscellaneous

- Especially designed for: Home office & Study, Living- & Bedroom
- Type: Table Lamp
- EyeComfort: No

Product dimensions and weight

- Net weight: 2.895 kg
- Height: 36.5 cm
- Length: 30.5 cm
- Width: 55.7 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 670 lm
- Mains power: Range 100 V – 240 V, 50–60 Hz
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 7 W
- Maximum wattage replacement bulb: 7 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water

- Class of protection: II – double insulated
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 8718696166666
- Net weight: 2.9 kg
- Gross weight: 3.34 kg
- Height: 98 mm
- Length: 199 mm
- Width: 554 mm
- Material number (12NC): 915005568101



Issue date: 2024-04-12
Version: 0.474

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com