

PHILIPS

Bulb 70W A60M E27

LED

6500K

806;380;140lm

15000h

8718696827376



One lamp. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cozy warm glow. All you need is your existing switch.

Create a warm atmosphere

- Three light settings from 2700 K to 2500 K to 2200 K

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- No dimmer or additional installation needed
- Instant on

Highlights

Three light settings


Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cozy light, while those with a higher Kelvin value produce a more energizing light. These new Scene Switch bulbs allow you to switch from functional lighting to natural light and to a cozy, warm dimmed light. Light levels can change from 100% to 40% to 10%. Now you can easily customize your room for a variety of tasks or adapt it to suit your mood.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Instant on

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No

Bulb dimensions

- Height: 11.1 cm
- Width: 6.1 cm

Durability

- Number of switch cycles: 100,000
- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 806-380-140 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes

Packaging information

- Product family: SceneSwitch

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 7.5, 2.5, 1 W
- Wattage equivalent: 60 W

Product dimensions and weight

- Length: 11.1 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696827376
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 15.3 cm
- Length: 6.5 cm
- Width: 7.2 cm
- Material number (12NC): 929001906727



Issue date: 2024-04-12
Version: 0.629

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com