

# PHILIPS

Filament Bulb Clear  
60W A60 E27

UltraEfficient

4000K

840lm

50000h

Light that's **easy**  
on your eyes



\*Designed for the comfort of your eyes.  
See below for more information.

8719514343801



## Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- Saves up to 90% Energy
- Long life bulb - Lasts up to 50 years

### Designed to be seen, looks good on and off

- Classic glass LED

# Highlights

## Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by

replacing your existing incandescent or halogen bulbs

## Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No

## Bulb dimensions

- Height: 10.5 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 500,000
- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 840 lm
- Warm-up time to 60% light: instant full light
- Color Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient

## Other characteristics

- Efficacy: 210 lm/W

## Packaging information

- EAN: 8719514343801
- EOC: 871951434380100
- Product title: LED CLA 60W A60 E27 4000K CL EELA SRT4

## Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 60 W
- Energy Efficiency Label (EEL): A
- Energy Consumption kWh/1000 h: 4

**Product dimensions and weight**

- Length: 10.5 cm

**Technical specifications**

- Frequency: 50-60 Hz
- EPREL Registration Number: 1370030

**Packaging dimensions and weight**

- EAN/UPC – product: 8719514343801
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2025-05-24  
Version: 0.182

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)