

PHILIPS

Bulb 70W A60M E27

LED

6500/3000K

880lm

15000h

8719514387829



One lamp. Your switch. Two light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cozy warm glow. All you need is your existing switch.

High quality light

- No visible flicker

Light beyond illumination

- No dimmer or additional installation needed

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 100,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000-6500 K
- Nominal luminous flux: 880 lm
- Luminous Efficacy (rated) (Nom): 110 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: SceneSwitch

Packaging information

- EAN: 8719514387829
- EOC: 871951438782900
- Product title: LED SSW A60 8-70W E27 WH-CDL 1PF/12 APR

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 70 W
- Power Consumption: 8 W

Product dimensions and weight

- Overall height: 111 mm
- Overall length: 111 mm
- Overall width: 61 mm

Technical specifications

- Frequency: 50-60

Packaging dimensions and weight

- EAN/UPC – product: 8719514387829
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2025-08-30
Version: 0.112

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com