

PHILIPS

Downlight

Recessed Lights

3000K

White



8720169260894



Twice the lifetime for long lasting performance

Designed with innovative thermal management for longer lifetime and reliable performance

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution

Safety

- No harmful UV radiation

Durability

- Long life span up to 30,000 hours

Highlights

Suitable for low ceilings
Slim design
Bright light with uniform distribution
 To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

No harmful UV radiation
 The product is designed to eliminate any potentially harmful UV radiation.

Long life span up to 30,000 hours
 Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 30 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 110
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 88

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 75 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.21 kg
- Recessed distance: 50 mm
- Overall height: 21 mm
- Overall length: 145 mm
- Overall width: 145 mm
- Recessed Ceiling cutout: 0 cm x 12.5 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Total lumen output fixture: 800
- Bulb technology: LED
- Light color: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: No
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169260894
- Net weight: 0.21 kg
- Gross weight: 0.25 kg
- Height: 17 cm
- Length: 3.8 cm
- Width: 17.8 cm



Issue date: 2026-06-13
Version: 0.152

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com