

# PHILIPS

## Becken Recessed Recessed Light

Recessed Lights

3000K

Metallic grey

8720169363120



## Superior light and style

Deep recessed for visual comfort

### Match your interior

- Expressive and elegant form

### Light effect

- Multiple layered visual effectDynamic tiered design

### Premium quality

- EyeComfort - light that's easy on the eyes

### Durability

- Long life span up to 25,000 hours

# Highlights

## Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

## Multiple layered visual effectDynamic tiered design

This dynamic tiered design makes for a striking impression that adds a creative touch to your rooms.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips s LED bulbs not only deliver

comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Grey
- Material: Plastic

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 24
- Color consistency: 5 SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 92

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office, Hall
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Lamp current: 60 mA

## Power consumption

- Power factor: 0.5
- Power: 7

## Product dimensions and weight

- Net weight: 0.1397 kg
- Recessed distance: 50 mm
- Overall height: 77 mm
- Recessed Ceiling cutout: 7.0–7.5 cm x 7.0–7.5 cm

## Service

- Warranty: 3 year(s)

### Technical specifications

- Diameter: 85 mm
- Total lumen output fixture: 650
- Bulb technology: LED
- Light color: Warm white light
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class II - Double Insulated
- Number of light sources: 1

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8720169363120
- Net weight: 0.14 kg
- Gross weight: 0.18 kg
- Height: 9.4 cm
- Length: 9.8 cm
- Width: 8.6 cm



Issue date: 2026-06-13  
Version: 0.86

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)