

PHILIPS

Eridani Recessed
Light 12W

Recessed Lights

4000K

White

Contemporary

8721103104373



Comfortable LED light that's easy on your eyes

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Uniform light distribution

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: No

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 110
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 80

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Home Office
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Contemporary

Other characteristics

- Lamp current: 85 mA

Power consumption

- Power factor: 0.5
- Wattage: 12 W

Product dimensions and weight

- Net weight: 0.194 kg
- Height: 3 cm
- Length: 17 cm
- Width: 17 cm
- Overall height: 34 mm
- Overall length: 173 mm
- Overall width: 173 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 960
- Bulb technology: LED
- Light color: Cool white light
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103104373
- Net weight: 0.19 kg
- Gross weight: 0.24 kg
- Height: 18 cm
- Length: 17.8 cm
- Width: 4 cm



Issue date: 2026-06-17
Version: 0.94

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com