

PHILIPS

Bulb 10W A60 E27

LED

6500K

1600lm

30000h

8721103131997



The light you love, now even brighter

Philips UltraBright LED bulbs combine exceptional brightness with superior comfort and efficiency. Delivering at least 40% more light than Philips Essential LED bulbs, they offer high-quality illumination for any space. Built to last up to 30,000 hours, so you won't have to worry about changing your bulbs often. EyeComfort technology ensures minimal glare and flicker to give you light that's easy on your eyes, with uniform light distribution for smooth, shadow-free illumination.

Choose for high quality light

- Light that's easy on your eyes
- Smooth and even lighting

Create the right light for your home

- High-quality bright light

Designed to last longer and save more energy

- Energy-efficient lighting
- Long lifetime of 30,000 hours

Highlights

Interlaced optics less glare

Interlaced optics technology is designed to give you light that's easy on your eyes by minimizing glare and flicker, with uniform light distribution for smooth, shadow-free lighting whether you're relaxing, reading or working.

Interlaced optics even lighting

Say goodbye to harsh shadows and bright spots. Philips Interlaced optics technology distribute light evenly for a comfortable, inviting atmosphere at home.

UltraBright 40% brighter

Philips UltraBright LED bulbs use new technology to deliver at least 40% more light than Philips Essential LED bulbs with comparable power consumption.

Saving energy 40%

Save energy at home with an LED bulb that uses the new technology to achieve a minimum efficacy of 160 lm/W.

long life time 30kh

Designed to last for an average of 30,000 hours, so you can avoid the hassle of frequent replacements and enjoy reliable, high-quality lighting for years to come.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Batteries included: No
- Choose your color: No
- LED integrated: Yes

Light characteristics

- Beam angle: 220
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1600 lm
- Warm-up time to 60% light: <0.5
- Luminous Efficacy (rated) (Nom): 160

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room
- Style: Classic
- EyeComfort: Yes
- LED Innovations: EyeComfort, UltraEfficient

Packaging information

- EAN: 8721103131997
- EOC: 872110313199700
- Product title: LEDBulb 10W E27 6500K 230V 1PF/12 B APR

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 112
- Power: 10

Product dimensions and weight

- Overall height: 113 mm
- Overall length: 113 mm
- Overall width: 60 mm

Service

- Warranty: 3 year(s)

Technical specifications

- Frequency: 50-60
- Diameter: 60 mm
- Bulb technology: LED
- Light color: Cool white light
- IP code: IP20

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103131997
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 11.9 cm
- Length: 6.3 cm
- Width: 6.3 cm



Issue date: 2026-07-04
Version: 0.20

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com