

# PHILIPS


## Eridani Recessed Light

Recessed Lights

3000K

White

8721103136411



## Comfortable light with a slimmer fit

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

### Easy installation

- Installation couldn't be simpler. Integrated clips on both sides of the fixture hold it in place, so no screw mounting is necessary. A GU10 connector cable makes it easy to attach a bulb.

### Durability

- Long life span up to 20,000 hours

# Highlights

## Easy to install

Installation couldn't be simpler. Integrated clips on both sides of the fixture hold it in place, so no screw

mounting is necessary. A GU10 connector cable makes it easy to attach a bulb.

## Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: No

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Number of switch cycles: 10,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 100
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 80

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Hallway
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Lamp current: 71 mA

## Power consumption

- Power factor: 0.51
- Power: 10

## Product dimensions and weight

- Net weight: 0.085 kg
- Cut out length: 12.5 cm
- Cut out width: 12.5 cm
- Recessed distance: 5 mm
- Overall height: 23 mm

## Service

- Warranty: 3 year(s)

## Technical specifications

- Diameter: 147 mm
- Total lumen output fixture: 800
- Bulb technology: LED
- Light color: 3000
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class II - Double Insulated
- Number of light sources: 1

## The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8721103136411
- Net weight: 0.09 kg
- Gross weight: 0.12 kg
- Height: 14.9 cm
- Length: 3.8 cm
- Width: 14.9 cm



Issue date: 2026-06-03  
Version: 0.154

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)