

PHILIPS

Meson Recessed Light

Recessed Lights

6500K

White

UltraBright

8721103157331



UltraBright downlight, provide bright and comfortable light solution for you

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Durability

- Long life span up to 30,000 hours

HIGH BRIGHTNESS AND WIDE BEAM ANGLE

- With 302 high-brightness LEDs, our solar floodlight produces 1200 lumens at a cool daylight color temperature of 6500K. Three adjustable heads can be rotated to ensure a wide 270° distribution of light and a range of up to 20m.

Light that's easy on your eyes

- Enjoy bright but comfortable light with our trusted EyeComfort technology. Illuminate your home and create the perfect ambience with LED lamps that are specially designed to minimize glare and flickering for maximum eye comfort.

Highlights

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

HIGH BRIGHTNESS AND WIDE BEAM ANGLE

With 302 high-brightness LEDs, our solar floodlight produces 1200 lumens at a cool daylight color temperature of 6500K. Three adjustable heads can be rotated to ensure a wide 270° distribution of light and a range of up to 20m.

Light that's easy on your eyes

Enjoy bright but comfortable light with our trusted EyeComfort technology. Illuminate your home and create the perfect ambience with LED lamps that are specially designed to minimize glare and flickering for maximum eye comfort.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: No

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 120

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Home Office, Hallway
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: UltraBright

Other characteristics

- Lamp current: 170 mA

Power consumption

- Power factor: 0.5
- Power: 21

Product dimensions and weight

- Net weight: 0.129 kg
- Cut out length: 17.5 cm
- Cut out width: 17.5 cm
- Recessed distance: 12 mm
- Overall height: 35 mm

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 190 mm
- Total lumen output fixture: 2520
- Bulb technology: LED
- Light color: Cool white light
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103157331
- Net weight: 0.13 kg
- Gross weight: 0.19 kg
- Height: 19.7 cm
- Length: 4.5 cm
- Width: 19.5 cm



Issue date: 2026-07-11
Version: 0.158

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com