

PHILIPS

Non integrated
compact fluorescent

PL-C

26 W

4 Pin

Warm white

927907383001



Long life and brilliant light

Philips' Bridge technology gives PLC sticks more light output than traditional PLCs. It also offers 10000hrs of life time, resulting in fewer replacements and lower maintenance costs.

Sustainable choice

- Saves energy

More light

- Philips bridge technology gives PLC bulbs more light output

Highlights

Saves energy Bright

Philips bridge technology gives PLC light bulbs more light output in

downlight lamps and light fixtures, making your home brighter.

Specifications

Bulb characteristics

- Dimmable: Yes
- Socket: 4 Pin

Durability

- Nominal lifetime: 10,000 hour(s)

Light characteristics

- Color rendering index (CRI): 82
- Light Color Category: Warm White
- Correlated Color Temperature (Nom): 3000
- Luminous Efficacy (rated) (Nom): 67 lm/W
- Luminous Flux: 1,800 lm

Power consumption

- Wattage: 26 W
- Power Consumption: 26.0 W

Technical specifications

- Light output: 1,800 lm
- Shape: Tube
- Dimmable: Yes
- Cap-Base: G24q-3

Packaging dimensions and weight

- EAN/UPC - product: 8711500623355
- Net weight: 60.4 g
- Gross weight: 69.11 g
- Height: 3.5 cm
- Length: 16.8 cm
- Width: 3.5 cm
- Material number (12NC): 927907383001



Issue date: 2024-02-14
Version: 0.596

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com