

# PHILIPS

Indoor Flood Light

DuraMax

65W

BR30

Medium Base

046677139278



## Brighten your home with infinite possibilities.

DuraMax Long Life bulbs last longer than standard incandescent bulbs, reducing the hassle of replacing burned out bulbs. Available in a variety of shapes and wattages, there is a DuraMax product to meet all your lighting needs.

### Light effect

- Provides a comfortable and relaxing environment

### Perfect Shape

- Ideal for recessed cans and track light fixtures

# Highlights

Soft white light

Use in indoor flood fixtures

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Light characteristics

- Application: Accent light

## Power consumption

- Voltage: 120 V
- Wattage: 65 W

## Technical specifications

- Lamp holder: BR30
- Number of lamps: 2
- Placement: Recessed cans, Track light
- Number of light sources: 2



Issue date: 2025-08-02  
Version: 0.599

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)