

PHILIPS

Tubular Fluorescent

20W

T12

Neutral

046677386931



Energy savings and long life.

Philips Linear Fluorescent bulbs offer long life and energy savings in an environmentally responsible light bulb. They come in Soft and Cool white, Natural light and Daylight Deluxe colors to help create the mood you desire in the room.

Long lifespan

- Lasts at least 9000 hours

Sustainable choice

- Reduced mercury for an environmentally friendly alternative

Use in any room in your home

- Pleasant light that is balanced for general purpose lighting

Highlights

Lasts at least 9000 hours

ALTO Lamp Technology

Ideal in offices or any room

Specifications

Bulb characteristics

- Intended use: Indoor

Light characteristics

- Application: Extra brightness
- Color rendering index (CRI): 73
- Light Color Category: Neutral
- Correlated Color Temperature (Nom): 3500
- Luminous Flux: 1,275 lm

Power consumption

- Wattage: 20 W
- Power Consumption: 20 W

Technical specifications

- Lamp holder: T12
- Number of lamps: 30
- Placement: Ceiling
- Cap-Base: G13 | Medium Bi-Pin
Fluorescent

Packaging dimensions and weight

- EAN/UPC - product: 046677386931
- Net weight: 0 kg
- Gross weight: 0.17 kg
- Height: 3.8 cm
- Length: 3.8 cm
- Width: 60.3 cm
- Material number (12NC): 927883073504



Issue date: 2024-07-25
Version: 0.533

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com