

PHILIPS

Mini-Reflector -
Spot

Halogen

50W

GU5.3

Sparkling light

Dimmable



046677415631



Brilliant alternative to incandescents

Philips 50W dimmable indoor halogen reflector spot provides bright sparkling accent light. An energy saving alternative to a 50W incandescent, it has no mercury, can last up to 2.7 years* and has an estimated yearly energy cost of \$6.02**.

Easy to use

- Dimmable
- Instant On

Bright white light

- Bright alternative to incandescent

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Alternative to incandescent

This halogen light bulb provides a bright, sparkling light, ideal for adding brilliance and drama to your home.

Instant On



Just by turning the switch, the light is at full brightness. No slow starting or waiting.

Specifications

Bulb characteristics

- Shape: Mini Reflector Spot
- Socket: GU5.3
- Base: GU5.3
- Lamp shape code: MRC16
- Dimmable: Yes

Power consumption

- Voltage: 12 V
- Power Consumption: 50

Rated values

- Rated lifetime: 3,000

Durability

- Average life (at 2.7 hrs/day): 2.7 year(s)
- Nominal lifetime: 3,000

Technical specifications

- Dimmable: Yes
- Cap-Base: GU5.3

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Color temperature: 3000 K
- Nominal luminous flux: 790 lm
- Correlated Color Temperature (Nom): 3000 K



Issue date: 2025-08-09
Version: 0.603

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com