

PHILIPS

Work and Security Light

300W

RSC

Sparkling light

Dimmable



046677415716



Brilliant alternative to incandescents

Philips 300W dimmable halogen linear light bulb provides bright light for work and security tasks. An efficient alternative to 300W incandescents, it has no mercury, can last 1.8 years* and has an estimated yearly energy cost of \$36.14**.

Easy to use

- Dimmable
- Instant On

Sparkling light

- Bright alternative to incandescent

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Alternative to incandescent

This halogen light bulb provides a bright, sparkling light, ideal for adding brilliance and drama to your home.

Instant On



Just by turning the switch, the light is at full brightness. No slow starting or waiting.

Specifications

Bulb characteristics

- Shape: Linear
- Base: RSC
- Lamp shape code: T3
- Bulb Finish: Clear
- Dimmable: Yes

Durability

- Average life (at 2.7 hrs/day): 1.8 year(s)
- Nominal lifetime: 2,000

Light characteristics

- Application: Extra brightness
- Color rendering index (CRI): 100
- Color temperature: 2900 K
- Nominal luminous flux: 5200 lm
- Correlated Color Temperature (Nom): 2900 K
- Luminous Flux: 5,000 lm
- Luminous Efficacy (rated) (Nom): 16 lm/W

Power consumption

- Voltage: 120 V
- Power Consumption: 300

Rated values

- Rated lifetime: 2,000

Technical specifications

- Dimmable: Yes
- Cap-Base: R7s



Issue date: 2025-08-30
Version: 0.606

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com