

PHILIPS

Indoor Flood Light

25W

MR16

GU10 Base

046677416935



Light for all of your specialized fixtures

Philips Specialty Incandescent and halogen bulbs provide the perfect light for accent and display lighting as well as general lighting in a variety of applications.

Light effect

- Provides a bright white light

Perfect Shape

- Ideal for recessed cans and track light fixtures

Highlights

Superior light quality

Use in indoor flood fixtures

Specifications

Bulb characteristics

- Intended use: Indoor
- Bulb Finish: Clear

Durability

- Nominal lifetime: 2,000

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Correlated Color Temperature (Nom): 2800

Power consumption

- Voltage: 120 V
- Power Consumption: 25

Rated values

- Rated lifetime: 2,000

Technical specifications

- Lamp holder: MR16
- Placement: Pendant fixtures, Recessed cans, Track light
- Dimmable: Yes
- Cap-Base: GU10
- Number of light sources: 1



Issue date: 2025-08-30
Version: 0.604

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com