

PHILIPS

Vanity Globe

Halogen

40w (60w)*

Medium base (E26)

Soft White Light

Dimmable

Lighting Facts/Datos de Iluminación

Per Bulb/Por Bombilla

Brightness/Brillo 540 lumens/lúmenes

Estimated Yearly Energy Cost/ \$4.82

Costo Estimado Anual de Energía

Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use./Basado en 3 hrs/día, 11¢/kWh. Costo depende de la tarifa y el uso.

Life/Duración 2.0 years/años

Based on 3 hrs/day/Basado en 3 hrs/día

Light Appearance/Apariencia de Iluminación

Warm/Cálida

Cool/Fría

2900 K

Energy Used/Usó de Energía 40 watts/vatios

046677433697



Energy savings without sacrifice

Philips 40W dimmable halogen globe provides bright, soft white light. An energy saving alternative to a 60W standard incandescent, it has no mercury, can last up to 2.3 years* and has an estimated yearly energy cost of \$4.82**.

Easy to use

- Dimmable
- Instant On

Soft white light

- Soft white alternative to incandescent

Energy efficiency

- Reduces energy costs

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience.

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.

Soft white light

This 40W decorative globe light bulb provides soft white light that is ideal for vanities and other decorative fixtures.

Reduces energy costs

This bulb saves up to 33%*** in electricity costs when compared to a 60W incandescent.

Specifications

Bulb characteristics

- Shape: Deco Globe
- Base: Medium Screw (E26)
- Lamp shape code: G25
- Dimmable: Yes

Bulb dimensions

- Width: 3.13 inch
- Height: 4.53 inch

Durability

- Average life (at 2.7 hrs/day): 2.3 year(s)
- Nominal lifetime: 2,500 hour(s)

Light characteristics

- Application: Sparkling light
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Soft White
- Nominal luminous flux: 500 lm

Power consumption

- Voltage: 120 V
- Wattage: 40 W
- Wattage equivalent: 60 W

Packaging dimensions and weight

- EAN/UPC – product: 046677433697
- Net weight: 0.13 kg
- Gross weight: 0.22 kg
- Height: 12.2 cm
- Length: 8.7 cm
- Width: 25.2 cm
- Material number (12NC): 925708036302



Issue date: 2024-03-31
Version: 0.539

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com