

# Lighting Facts/Datos de Illuminación Per Bulb/Por Bombilla Brightness/Brillo 540 lumens/lúmenes Estimated Yearly Energy Cost/\$4.82 Costo Estimated Anual de Energía Based on 3 hrs/day, 11¢/k/Wh. Cost depends on rates and use./Basado en 3 hrs/día, 11¢/k/Wh. Costo depende de la tarifa y el uso. Life/Duración Based on 3 hrs/day/Basado en 3 hrs/día Light Appearance/Apariencia de Illuminación Warm/Cálida Cool/Fría 2900 K Energy Used/Uso de Energía 40 watts/vatios

046677433697



# Energy savings without sacrifice

Philips 40W dimmable halogen globe provides bright, soft white light. An energy saving alternative to a 60W standard incandescent, it has no mercury, can last up to 2.3 years\* and has an estimated yearly energy cost of \$4.82\*\*.

### Easy to use

- Dimmable
- · Instant On

### Soft white light

· Soft white alternative to incandescent

### **Energy efficiency**

· Reduces energy costs

# Highlights

### **Dimmable**

This bulb can be used with most dimmers to create your desired ambience.

### **Instant On**

Just by turning the switch, your room is at full brightness. No slow starting or waiting.

### Soft white light

This 40W decorative globe light bulb provides soft white light that is ideal for vanities and other decorative fixtures.

### **Reduces energy costs**

This bulb saves up to 33%\*\*\* in electricity costs when compared to a 60W incandescent.

## Specifications

### **Bulb characteristics**

Shape: Deco GlobeBase: Medium Screw (E26)

· Lamp shape code: G25

· Dimmable: Yes

### **Bulb dimensions**

Width: 3.13 inchHeight: 4.53 inch

### **Durability**

 Average life (at 2.7 hrs/day): 2.3 year(s)

· Nominal lifetime: 2,500 hour(s)

### **Light characteristics**

Application: Sparkling light
Color rendering index (CRI): 100
Color temperature: 2800 K
Light Color Category: Soft White
Nominal luminous flux: 500 lm

### **Power consumption**

Voltage: 120 VWattage: 40 W

• Wattage equivalent: 60 W



Issue date: 2024-09-04 Version: 0.540 © 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.