

PHILIPS

LEDtube Type A T8

LED

1200mm

4000K

G13

046677542108



Simple T8 LED replacement for fluorescent tubes

Philips InstantFit LED tubes easily replace fluorescent T8 tubes operated on instant-start electronic ballasts, no rewiring needed. This glass LED linear bulb looks and feels like fluorescent and has a cool white light and long lifetime.

High quality light

- Cool, white light

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Instant on

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T8
- Socket: G13
- Type of glass: Frosted
- Lamp shape code: T8
- Control: On/off switch
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

Bulb dimensions

- Height: 121.23 cm
- Width: 2.78 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 36,000 hour(s)

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1800 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 112 lm/W

Packaging information

- Product family: UniversalFit
- EAN: 046677542108
- Product title: 16T8/LED/48-840/IF18/G 10/1 FB

Power consumption

- Power factor: >0.9
- Voltage: 120-277, 347 V
- Wattage: 16 W
- Wattage equivalent: 25;28;30;32 W

Product dimensions and weight

- Length: 121.23 cm

Technical specifications

- Frequency: 20-120 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677542108
- Net weight: 0.44 kg
- Gross weight: 0.58 kg
- Height: 3 cm
- Length: 123.3 cm
- Width: 3 cm
- Material number (12NC): 929001960633



Issue date: 2024-03-29
Version: 0.265

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com