

PHILIPS

Bulb (Dimmable)

LED

7.2W-65W

E26

Daylight

Dimming

046677548100



Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Dimmable: Yes
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 90 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 5000 K
- Luminous Flux: 650 lm
- Luminous Efficacy (rated) (Nom): 90.00 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 046677548100
- EOC: 548107
- Product title: 7.2BR30/PER/950/P/E26/DIM 6/1FB T20

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: >0.7
- Voltage: 120 V
- Wattage equivalent: 65 W
- Power Consumption: 7.2 W

Product dimensions and weight

- Overall height: 5-1/4 inch
- Overall length: 4-1/4 inch
- Overall width: 3-3/4 inch

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50
- Diameter: 3-3/4 inch
- Dimmable: Yes
- Line Frequency: 60
- Cap-Base: E26 | Single Contact
Medium Screw
- UL Wet/ damp/ dry location: Damp
location

Packaging dimensions and weight

- EAN/UPC – product: 046677548100
- Net weight: 0.06 kg
- Gross weight: 0.14 kg
- Height: 13.1 cm
- Length: 9.1 cm
- Width: 9.1 cm



Issue date: 2025-08-30
Version: 0.277

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com