

# PHILIPS

Bulb (Dimmable)

LED

7.2W-65W

E26

Daylight

Dimming

046677548100



## Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Choose for a sustainable solution**

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

# Highlights

## Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -4 to +113 °F
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 90
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: 0.5
- Correlated Color Temperature (Nom): 5000
- Luminous Flux: 650 lm
- Luminous Efficacy (rated) (Nom): 90.00

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677548100
- EOC: 548107
- Product title: 7.2BR30/PER/950/P/E26/DIM 6/1FB T20

## Power

- Power Factor (Fraction): 0.7

**Power consumption**

- Power factor: >0.7
- Voltage: 120 V
- Wattage equivalent: 65
- Power: 7.2

**Product dimensions and weight**

- Overall height: 5-1/4 inch
- Overall length: 4-1/4 inch
- Overall width: 3-3/4 inch

**Rated values**

- Rated lifetime: 15,000

**Technical specifications**

- Frequency: 50
- Diameter: 3-3/4 inch
- Bulb technology: LED
- Dimmable: Yes
- Line Frequency: 60
- Cap-Base: E26
- UL Wet/ damp/ dry location: Damp location
- can it be used in closed luminaires: Yes

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677548100
- Net weight: 0.06 kg
- Gross weight: 0.14 kg
- Height: 13.1 cm
- Length: 9.1 cm
- Width: 9.1 cm



Issue date: 2026-06-24  
Version: 0.277

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)