

PHILIPS

Filament Candle
Clear 40W B11 E26

LED

2700-2200K

300lm

15000h

Dimming

046677549589



The right light makes the moment

Philips LEDs with a dimmable warm glow effect, enables light levels to dim to the warm tones of traditional bulbs. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

Add a beautiful sparkle to your home

- Classic glass LED

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Glass Design

The look you love, the performance you expect. Classic glass designs replicate the beautiful.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: B11
- Socket: E26
- Type of glass: Clear
- Dimmable: Yes
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 9.2 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700-2200 K
- Nominal luminous flux: 300 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 2700, 2200 K
- Luminous Flux: 300 lm
- Luminous Efficacy (rated) (Nom): 90.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 90 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677549589
- EOC: 549584
- Product title: 3.3B11/PER/927-922/CL/G/E26/WGX1FB T20

Power

- Power Factor (Fraction): 0.75

Power consumption

- Energy Star Certified: Yes
- Power factor: 0.75
- Voltage: 120 V
- Wattage: 3.3 W
- Wattage equivalent: 40 W
- Power Consumption: 3.3 W

Product dimensions and weight

- Length: 9.2 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: Yes
- Cap-Base: E26 | Single Contact Medium Screw
- UL Wet/ damp/ dry location: Wet location

Packaging dimensions and weight

- EAN/UPC – product: 046677549589
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 11 cm
- Length: 4.5 cm
- Width: 4.5 cm
- Material number (12NC): 929002047204



Issue date: 2024-04-22
Version: 0.212

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com