



Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

• Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

· Intended use: Indoor/Outdoor

Lamp shape: BA11Socket: E26Dimmable: YesBulb Finish: ClearBulb Material: Glass

Durability

· Number of switch cycles: 20,000

• Ambient temperature range: -4 °F to

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Beam angle: 300 degree(s)

Color rendering index (CRI): 95

· Color temperature: 5000 K

• Cotol temperature. 5000 K

Nominal luminous flux: 500 lm
Warm-up time to 60% light: 0.4 s

• Warm up time to 00% tight. 0.1

• Color Code: 950 | CCT of 5000K

 Correlated Color Temperature (Nom): 5000 K

· Luminous Flux: 500 lm

 Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

· Extra Features: Dimmable

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 046677564926

• EOC: 564922

 Product title: 5BA11/PER/ UD50/CL/G/E26/D 6/3PF T20

Power

• Power Factor (Fraction): 0.7

Power consumption

Power factor: 0.7Voltage: 120 V

Wattage equivalent: 60 WPower Consumption: 5 W

Product dimensions and weight

Overall height: 3-15/16 inch
Overall length: 3-15/16 inch
Overall width: 1-3/8 inch

Rated values

· Rated lifetime: 15,000

Technical specifications

• Frequency: 60

· Diameter: 1-3/8 inch

• Dimmable: Only with specific

dimmers

Line Frequency: 60

· Cap-Base: E26 | Single Contact

Medium Screw

 $\boldsymbol{\cdot}$ UL Wet/ damp/ dry location: Wet

location

 $\boldsymbol{\cdot}$ can it be used in closed luminaires:

No

Packaging dimensions and weight

• EAN/UPC - product: 046677564926

Net weight: 0.06 kgGross weight: 0.11 kgHeight: 17.1 cm

Length: 4.6 cmWidth: 13 cm

