

PHILIPS

Filament Bulb Amber
60W A19 E26

LED


2000K

400lm

15000h

Dimming

046677565794



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Designed to be seen, looks good on and off

- Vintage style LED

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Vintage (2000K & 2200K)

Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional color and amber glow of old-fashioned incandescent lighting. The clear amber tinted glass bulb, brass finish base, and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cozy and warm ambience.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Amber
- Dimmable: Yes

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 330
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Nominal luminous flux: 400 lm
- Luminous Efficacy (rated) (Nom): 61

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Decorative, Dimmable

Packaging information

- EAN: 046677565794
- EOC: 565796
- Product title: 6.5A19/VIN/820/E26/Amber/G/SP D 4/1PFT20

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 60
- Power: 6.5

Product dimensions and weight

- Overall height: 7/16 inch
- Overall length: 7/16 inch
- Overall width: 1/4 inch

Technical specifications

- Frequency: 60
- Bulb technology: LED
- can it be used in closed luminaires: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677565794
- Net weight: 0.03 kg
- Gross weight: 0.06 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm



Issue date: 2026-05-14
Version: 0.143

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com