

PHILIPS

Filament Candle Clear
40W BA11 E12 x3

LED

2200-2700K

300lm

15000h

Dimming

046677566661



Clear LED candle bulbs add a sparkle to your home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: BA11
- Socket: E12
- Type of glass: Clear
- Bulb Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

Bulb dimensions

- Height: 11.1 cm
- Width: 3.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Nominal luminous flux: 300 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 85 lm/W

Packaging information

- EAN: 04667756661
- EOC: 566661
- Product title: 3.5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20

Power consumption

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W

Product dimensions and weight

- Length: 11.1 cm

Technical specifications

- Frequency: 60 Hz

046677566661

Packaging dimensions and weight

- EAN/UPC - product: 046677566661
- Net weight: 0.04 kg
- Gross weight: 0.09 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 13 cm
- Material number (12NC): 929002990703



Issue date: 2024-04-11
Version: 0.55

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com