

PHILIPS

Reflector PAR38
E26

LED

-

-

10950h

046677568276



State-of-the-art LED for the home

Party light for creating nice atmosphere at home

Specifications

General

- Suitable For Accent Lighting: Yes

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

Durability

- Number of switch cycles: 10,000
- Ambient temperature range: -4 °F to 113 °F
- Nominal lifetime: 10,950

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Color rendering index (CRI): -
- Warm-up time to 60% light: 0.5 s

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 046677568276
- EOC: 568279
- Product title: 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: 120 V
- Power: 13.5

Product dimensions and weight

- Overall height: 5-1/4 inch
- Overall length: 5-1/4 inch
- Overall width: 4-13/16 inch

Rated values

- Rated lifetime: 10,950

Technical specifications

- Frequency: 60
- Diameter: 4-13/16 inch
- Bulb technology: LED
- Dimmable: No
- Line Frequency: 60
- Cap-Base: E26
- UL Wet/ damp/ dry location: Wet location
- can it be used in closed luminaires: Yes

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677568276
- Net weight: 0.35 kg
- Gross weight: 0.44 kg
- Height: 20.9 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2026-05-13
Version: 0.97

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com