

PHILIPS

Reflector PAR38
E26

LED

-

-

10950h

046677568283



State-of-the-art LED for the home

Party light for creating nice atmosphere at home

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

Bulb dimensions

- Height: 13.2 cm
- Width: 12.2 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 10,000
- Nominal lifetime: 10,950 hour(s)
- Ambient temperature range: -4 °F to 113 °F

Light characteristics

- Color rendering index (CRI): -
- Warm-up time to 60% light: 0.5 s

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 046677568283
- EOC: 568287
- Product title: 13.5PAR38/PER/
GREEN/G/E26/ND/ULW 3/1PF

Power

- Power Factor (Fraction): 0.5

Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 13.5 W
- Power Consumption: 13.5 W

Product dimensions and weight

- Length: 13.2 cm

Rated values

- Rated lifetime: 10,950 hour(s)

Technical specifications

- Frequency: 60 Hz
- Line Frequency: 60 Hz
- Dimmable: No
- Cap-Base: E26 | Single Contact
Medium Screw
- UL Wet/ damp/ dry location: Wet
location

Packaging dimensions and weight

- EAN/UPC – product: 046677568283
- Net weight: 0.35 kg
- Gross weight: 0.44 kg
- Height: 20.9 cm
- Length: 13 cm
- Width: 13 cm
- Material number (12NC):
929001306763



Issue date: 2024-03-29
Version: 0.58

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com