

PHILIPS

LEDtube Type B T8

LED

1200mm

3000/3500/4000/5000/6500
K

G13

046677568511



LED tube that works directly from your power line

Eliminate ballast maintenance with Philips MainsFit LED tubes. This T8 tube is designed to replace T8 and T12 tubes on shunted and non-shunted sockets, looks and feels like fluorescent, and can select color light 3000K, 3500K, 4000K, 5000K or 6500K by dipswitch with long lifetime.

Choose a simple replacement for your old bulbs

- Perfect replacement T8 linear fluorescent application
- Double-Ended Installation

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Highlights

Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

MainsFit Double-Ended

Philips MainsFit LED tubes are double-ended and can be installed in either direction.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T8
- Socket: G13
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Glass

Bulb dimensions

- Height: 121.23 cm
- Width: 2.78 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 hour(s)

Light characteristics

- Beam angle: 240 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000K/3500K/4000K/5000K/6500 K
- Nominal luminous flux: 1800 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): Selectable, 3000, 3500, 4000, 5000, 6500 K
- Luminous Flux: 1,800 lm
- Luminous Efficacy (rated) (Nom): 128.00 lm/W

Miscellaneous

- Approval Marks: RoHS compliance, UL certificate, DLC compliance

Other characteristics

- Efficacy: 128 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677568511
- EOC: 568519
- Product title: 14T8/LED/48-5CCT/MF18/G/DS 1/10

Power

- Power Factor (Fraction): 0.9

Power consumption

- Power factor: 0.9
- Voltage: 120-277 V
- Wattage: 14 W
- Wattage equivalent: 32 W
- Power Consumption: 14 W

Product dimensions and weight

- Length: 121.23 cm

Rated values

- Rated lifetime: 50,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap-Base: G13 | Medium Bi-Pin Fluorescent

Packaging dimensions and weight

- EAN/UPC - product: 046677568511
- Net weight: 2.15 kg
- Gross weight: 3 kg
- Height: 8.4 cm
- Length: 125 cm
- Width: 17.4 cm
- Material number (12NC): 929003051333



Issue date: 2024-03-29
Version: 0.18

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com