

PHILIPS

Bulb


LED

4W-40W

E26

Orange

046677568849



Brighten your home with infinite possibilities.

Philips LED energy-saving colored bulbs provide instant brightness and make colors appear more vivid. Ideal for special activities and occasions.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Saves up to 80% Energy

Light beyond illumination

- Colored Bulbs Classic Glass

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect

sustainable replacement for traditional standard incandescent bulbs.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Brilliant Colors (Glass)

Festive LED colored bulbs to decorate your home with bright colors for holidays and special occasions. Colored glass ensures high saturation for even brighter colors, for use both indoor and out.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Dimmable: No
- Bulb Finish: Orange
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -4 °F to 113 °F
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Warm-up time to 60% light: 0.5 s

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 046677568849
- EOC: 568840
- Product title: 4A19/PER/ORANGE/G/E26/ND 4/1PF

Power

- Power Factor (Fraction): 0.40

Power consumption

- Power factor: 0.4
- Voltage: 120 V
- Wattage equivalent: 40 W
- Power Consumption: 4 W

Product dimensions and weight

- Overall height: 4-3/16 inch
- Overall length: 4-3/16 inch
- Overall width: 2-3/8 inch

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 60
- Diameter: 2-3/8 inch
- Dimmable: No
- Line Frequency: 60
- Cap-Base: E26 | Single Contact
Medium Screw
- UL Wet/ damp/ dry location: Wet
location
- can it be used in closed luminaires:
No

Packaging dimensions and weight

- EAN/UPC – product: 046677568849
- Net weight: 0.03 kg
- Gross weight: 0.09 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm



Issue date: 2025-09-13
Version: 0.51

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com